



Fiery® E11
Fiery FS400 Pro

Faster processing. Exceptional quality. Built-in intelligence.

The Fiery E11 for the FUJIFILM Business Innovation Revoria Press™ E1136 / E1125 / E1110 / E1100 delivers faster processing speeds, outstanding image quality, and time-saving workflows.

A more productive print room

The Fiery server delivers performance-boosting features so you can get more jobs printed, faster. Increase efficiency with the automation benefits from the included, browser-based Fiery JobFlow™ Base software.

Differentiate with personalisation

Fiery FreeForm™ Create, an included application, allows you to quickly and simply create personalised jobs for print production. Add variable elements such as text, images, or barcodes with just a few clicks.

Built-in print intelligence

Reduce setup time and cut waste with Fiery JobExpert™ — a built-in feature in Fiery Command WorkStation® — that automatically analyses incoming PDF files and dynamically chooses optimal Fiery print settings.

A unified, integrated print room

Manage all your Fiery Driven™ cutsheet and wide format printers from Fiery Command WorkStation to centralise job management. Integrate your print production workflow with management information systems, Web-to-Print systems, and popular prepress workflows for end-to-end automation.

Use the Fiery Workflow Suite of integrated products, like Fiery Impose, Compose, or JobMaster™ to accelerate makeready from job setup through production in one single, visual interface.

Achieve superior image quality

Perform grayscale calibration to preserve and enhance shadow detail. Inspect jobs in the optional Fiery ImageViewer for Black and White and make black curve adjustments to optimise image quality and save them for future use.



Fiery® E11 specifications

Fiery Driven™ engines

- Revoria Press™ E1136 / E1125 / E1110 / E1100
- Supports all engine finishing devices

Hardware and platform

- Intel® Core™ i3-8100 Processor, 3.60 GHz
- 8 GB RAM
- SSD boot drive for OS & Fiery software
- 500 GB HDD
- USB 3.0: 2 rear ports, 3 on Fiery QuickTouch™ panel
- Microsoft Windows® 10 IoT Enterprise 2019 LTSC
- Fiery FS400 Pro system software
- Fiery Installer Builder

Productivity and workflow

- Fiery Command WorkStation®
- Fiery JobExpert™
- Fiery drivers for Linux, Windows and Mac®
- Fiery Essential Driver
- Fiery server presets
- Booklet Maker
- Pad printing
- Copy numbering
- Fiery Hot Folders/Virtual Printers
- Direct mobile printing
- Fiery Go (Android™ and iOS)
- EFI IQ: Dashboard, Insight, Notify, Go

Document preparation

- Fiery VUE
- Fiery JobFlow™ Base
- Fiery Impose (option)
- Fiery Compose (option)
- Fiery JobMaster™ (option)
- Booklet Maker
- Fiery Paper Catalog

Fiery imaging technology

- Job based calibration
- Calibration guard
- Black custom screening
- Image smoothing
- Fiery grayscale calibration
- Fiery ImageViewer for black and white (optional)

Adobe interpreter support

- CPSI version 3020
- Adobe® PDF Print Engine® 5.3**

Performance

- Fiery SmartRIP
- Spool-RIP-print simultaneously
- Strict ordered printing

Variable data printing

- Fiery FreeForm™ Create
- Supported file formats:
 - Fiery FreeForm Plus
 - PPML v2.x/3.0
 - PDF/VT 1 and 2
 - Creo VPS
- VDP Record and Set Level Finishing
- VDP Record Range Printing
- Define Record Length
- VDP Resource Manager
- VDP Raster Preview

File format support

- Adobe® PostScript® Levels 1, 2, 3
- Adobe PDF
- Encapsulated PostScript (EPS)
- MS Office document formats: doc, xls, ppt, pub (via Hot Folders)

Integration

- JDF v1.7
- Fiery API
- MIS and Web-to-Print integration ready
- Prepress workflow integration (Agfa® Apogee, Kodak® PRINERGY, Heidelberg® Prinect, SCREEN EQUIOS)

Security

- Secure Erase
- Security profiles
- FIPS 140-2 compliant data encryption
- ISO/IEC 15408 & IEEE Std 2600 (Common Criteria) compliant***
- Port-based access controls
- 802.1x advanced authentication methods
- USB security
- Port blocking
- IP filtering
- IPsec network encryption
- Secure connections using HTTPS with support for TLS 1.3
- Secure Printing
- Digitally signed software updates
- Windows 10 OS security features
- Authentication/Accounting

Networking/Connectivity

- TCP/IP, AppleTalk, Bonjour support, SNMP, Port 9100, IPP, FTP, SMB, WSD, point and print, print via email (PS/PDF), IPv6 support, LDAP authentication

EMC

- FCC Title 47, Part 15 Subpart B.
- ISED of Canada, ICES-003.
- EN55032: 2015 +A11:2020
- EN 55035: 2017/A11:2020
- AS/NZS CISPR 32: 2013.
- CCC-China
- KC-Korea
- BSMI-Taiwan

Safety

- CB Scheme-IEC-62368-1, 2nd Edition
- EN 62368-1, 2nd Edition,
- CE Mark (EU)
- cTUVus -NA
- CCC - China
- BSMI-Taiwan

Power supply and consumption

- 100–240 VAC, 50/60 Hz, 1.5A
- Maximum / typical power usage: 80W / 30 W

Dimensions/Weight

- 9.75 x 15.10 x 8.0 in (D x H x W) (248 x 384 x 203 mm)
- 13.0 lbs (59 kg)

Optional Fiery software and hardware

- Fiery IPDS
- Fiery ImageViewer for Black and White
- EFI ES-3000 spectrophotometer
- Fiery Impose®
- Fiery Impose-Compose
- Fiery Compose*
- Fiery JobMaster*
 - Available as a 5-year term license
- Fiery JobMaster-Impose
 - Available as a 5-year term license
- Fiery NX One Station
- Fiery disk drive security kits
- Adobe® Acrobat® Pro 2020 Kit

* Free 30-day trial available

** Updated with enhancements and service releases on an ongoing basis

*** With proper configuration by end customer or service provider



FUJIFILM Business Innovation Singapore Pte. Ltd.

Authorized Distributor

20E Pasir Panjang Road #02-21A Mapletree Business City Singapore 117439
Tel. +65-6766-8888

fujifilm.com/fbsg

Electronics For Imaging

6453 Kaiser Drive
Fremont, CA 94555

efi.com/fiery

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •Revoria, Revoria logo and Revoria Press are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

Nothing herein should be construed as a warranty in addition to the express warranty statement provided with EFI products and services. ColorGuard, ColorRight, Command WorkStation, EFI, the EFI logo, Electronics For Imaging, Fiery, the Fiery logo, Fiery Compose, Fiery Driven, the Fiery Driven logo, Fiery Edge, Fiery Impose, Fiery ImageViewer, Fiery Intensify, Fiery JobExpert, Fiery JobFlow, Fiery JobMaster, Fiery Prints, the Fiery Prints logo, FreeForm, IQ, RIPChips, RIP-While-Print, Spot-On, Spot Pro, and WebTools are trademarks or registered trademarks of Electronics For Imaging, Inc. and/or its wholly owned subsidiaries in the U.S. and/or certain other countries. All other terms and product names may be trademarks or registered trademarks of their respective owners and are hereby acknowledged.